

Part No: 859-040

Schedule 80 PVC & CPVC

Union

Desc: 4 PVC UNION SOCXFPT FKM

MSRP: 460.49

Part Code: 080

Weight(lbs): 3.915

Weight(kg): 1.776

Weight(gm): 1776


Size: 4"

Color: GRAY

Material: PVC

Connection Socket x Fipt

O-Ring FKM



L = 5- 7/8

M = 5-13/32

N = 1- 7/8

NUT = 7-1/8
O.D.

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; ± 1/32 inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; ± 1/32 inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; ± 1/32 inch

L = Overall length of fittings; ± 1/16 inch.

M = Outside diameter of socket/thread hub; ± 1/16 inch.

N = Socket bottom to socket bottom; couplings; ± 1/16 inch.

W = Height of cap; ± 1/16 inch

Typical Molded Dimension References

