

Part No: 859-040SR

Schedule 80 PVC & CPVC

Union

Desc: 4 PVC UNION SOCXSRFPT FKM

MSRP: 252.52

Part Code: 086

Weight(lbs): 3.971

Weight(kg): 1.801

Weight(gm): 1801


Size: 4"

Color: GRAY

Material: PVC

Connection Socket x SR Fipt

O-Ring FKM



L = 5-15/16

M = 5-13/32

N = 2-7/32

NUT = 7-1/8
O.D.

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/32$ inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; $\pm 1/32$ inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/32$ inch

L = Overall length of fittings; $\pm 1/16$ inch.

M = Outside diameter of socket/thread hub; $\pm 1/16$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/16$ inch.

W = Height of cap; $\pm 1/16$ inch

Typical Molded Dimension References

