

Part No: 866V-250

Schedule 80 PVC & CPVC

Clamp-On Saddle

Desc: 2X1-1/4 PVC CLAMP SADDLE SOC FKM ZNC BLT

MSRP: 57.1

Part Code: 086

Weight(lbs): 0.694

Weight(kg): 0.315

Weight(gm): 315

Size: 2"X1-1/4"

Color: GRAY

Material: PVC

Connection Single Socket

Type Clamp Saddle

Hardware Zinc

O-Ring FKM



H = 2-13/16

H1 = 1-1/2

L = 2-7/16

L1 = 3-7/16

M = 2-1/16

N = 5/16

No of Bolts = 4

Bolt = 8

Hole Size = 1-1/2

Torque
FT./LBS.

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; ± 1/32 inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; ± 1/32 inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; ± 1/32 inch

L = Overall length of fittings; ± 1/16 inch.

M = Outside diameter of socket/thread hub; ± 1/16 inch.

N = Socket bottom to socket bottom; couplings; ± 1/16 inch.

W = Height of cap; ± 1/16 inch

Typical Molded Dimension References



The information printed here is based on current information & product design at the time of publication and is subject to change without notification. Spears® ongoing commitment to product improvement may result in some variation. No representation, guarantees or warranties of any kind are as to its accuracy, suitability for particular application or results to be obtained therefrom. For verification of technical data or additional information, please contact Spears® Technical Service Department :: WEST COAST : (818) 364-1611 - EAST COAST : (717) 938-9006