

Part No: 866V-523C

Schedule 80 PVC & CPVC

Clamp-On Saddle

Desc: 6X1/2 CPVC CLAMP SADDLE SOC FKM ZN BLT

MSRP: 265.08

Part Code: 096

Weight(lbs): 2.619

Weight(kg): 1.188

Weight(gm): 1188

Size: 6"X1/2"

Color: GRAY

Material: CPVC

Connection Single Socket

Type Clamp Saddle

Hardware Zinc

O-Ring FKM



H = 5-3/8

H1 = 3-13/16

L = 3

L1 = 8-3/16

M = 1-11/16

N = 1-1/8

Bolt = 8

Hole Size = 1-1/8

No of = 4

Torque
FT./LBS.

Bolts

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; ± 1/32 inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; ± 1/32 inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; ± 1/32 inch

L = Overall length of fittings; ± 1/16 inch.

M = Outside diameter of socket/thread hub; ± 1/16 inch.

N = Socket bottom to socket bottom; couplings; ± 1/16 inch.

W = Height of cap; ± 1/16 inch

Typical Bushing Dimension References

