

Part No: 866V-532

Schedule 80 PVC & CPVC

Clamp-On Saddle

Desc: 6X4 PVC CLAMP SADDLE SOC FKM ZINC BOLT

MSRP: 217.88

Part Code: 086

Weight(lbs): 5.397

Weight(kg): 2.448

Weight(gm): 2448

Size: 6"X4"

Color: GRAY

Material: PVC

Connection Single Socket

Type Clamp Saddle

Hardware Zinc

O-Ring FKM



H = 6

Bolt = 10
Torque
FT./LBS.

Hole Size = 4

No of = 4
Bolts

H1 = 3-13/16

L = 6-1/16

L1 = 9-13/16

M = 5-1/4

N = 7/16

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; ± 1/32 inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; ± 1/32 inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; ± 1/32 inch

L = Overall length of fittings; ± 1/16 inch.

M = Outside diameter of socket/thread hub; ± 1/16 inch.

N = Socket bottom to socket bottom; couplings; ± 1/16 inch.

W = Height of cap; ± 1/16 inch

Typical Molded Dimension References

