

Part No: 866V-579

Schedule 80 PVC & CPVC

Clamp-On Saddle

Desc: 8X2-1/2 PVC CLAMP SADDLE SOC FKM ZN BL

MSRP: 355.08

Part Code: 086

Weight(lbs): 9.681

Weight(kg): 4.391

Weight(gm): 4391

Size: 8"X2-1/2"

Color: GRAY

Material: PVC

Connection Single Socket

Type Clamp Saddle

Hardware Zinc

O-Ring FKM



H = 7-5/8

H1 = 4- 7/8

No of Bolts = 6

L = 8-15/32

L1 = 10-1/16

M = 5-1/4

N = 1-1/2

Bolt Torque = 10

Hole Size = 4

FT./LBS.

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; ± 1/32 inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; ± 1/32 inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; ± 1/32 inch

L = Overall length of fittings; ± 1/16 inch.

M = Outside diameter of socket/thread hub; ± 1/16 inch.

N = Socket bottom to socket bottom; couplings; ± 1/16 inch.

W = Height of cap; ± 1/16 inch

Typical Bushing Dimension References

