

Part No: 867SV-532SR

Schedule 80 PVC & CPVC
Clamp-On Saddle
Desc: 6X4 PVC CLAMP SADDLE SRFPT FKM SS BOLT

MSRP: 315.84

Part Code: 086

Weight(lbs): 5.567

Weight(kg): 2.525

Weight(gm): 2525

Size: 6"X4"

Color: GRAY

Material: PVC

Connection Single SR Fipt

Type Clamp Saddle

Hardware SS

O-Ring FKM

 $N = 1-3/16$
Bolt = 10
Torque
FT./LBS.
Hole Size = 4

No of = 4
Bolts
H = 6

 $H1 = 3-13/16$
 $L = 6-1/16$
 $L1 = 9-13/16$
 $M = 5-1/4$

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/32$ inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; $\pm 1/32$ inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/32$ inch

L = Overall length of fittings; $\pm 1/16$ inch.

M = Outside diameter of socket/thread hub; $\pm 1/16$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/16$ inch.

W = Height of cap; $\pm 1/16$ inch

Typical Molded Dimension References

