

**Part No:** 868-335

**Schedule 80 PVC & CPVC**

**Clamp-On Saddle**

**Desc:** 3X1 PVC CLAMP SADDLE D/O SOC EPDM ZN BL

**MSRP:** 88.99

**Part Code:** 086

**Weight(lbs):** 0.985

**Weight(kg):** 0.447

**Weight(gm):** 447

**Size:** 3"X1"

**Color:** GRAY


**Material:** PVC

**Connection** Double Socket

**Type** Clamp Saddle

**Hardware** Zinc

**O-Ring** EPDM



**H** = 3-3/16

**L** = 3

**L1** = 4-3/4

**M** = 1-11/16

**N** = 9/32

**Hole Size** = 1-1/8

**Bolt** = 8  
**Torque**  
**FT./LBS.**

**No of** = 4  
**Bolts**

## Injection Molded Dimension References:

**G** = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; ± 1/32 inch.

**H** = Intersection of center lines to face of fitting; 90° elbows tees, crosses; ± 1/32 inch.

**J** = Intersection of center lines to bottom of socket/thread; 45° elbows; ± 1/32 inch

**L** = Overall length of fittings; ± 1/16 inch.

**M** = Outside diameter of socket/thread hub; ± 1/16 inch.

**N** = Socket bottom to socket bottom; couplings; ± 1/16 inch.

**W** = Height of cap; ± 1/16 inch

## Typical Molded Dimension References

