

Part No: 868-417C

Schedule 80 PVC & CPVC

Clamp-On Saddle

Desc: 4X1 CPVC CLAMP SADDLE D/O SOC EPDM ZN BL

MSRP: 187.21

Part Code: 096

Weight(lbs): 1.404

Weight(kg): 0.637

Weight(gm): 637

Size: 4"X1"

Color: GRAY


Material: CPVC

Connection Double Socket

Type Clamp Saddle

Hardware Zinc

O-Ring EPDM



H = 3-27/32

L = 3

L1 = 5-13/16

M = 1-11/16

N = 13/32

Bolt = 8

No of = 4

Hole Size = 1-1/8

Torque
FT./LBS.

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; ± 1/32 inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; ± 1/32 inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; ± 1/32 inch

L = Overall length of fittings; ± 1/16 inch.

M = Outside diameter of socket/thread hub; ± 1/16 inch.

N = Socket bottom to socket bottom; couplings; ± 1/16 inch.

W = Height of cap; ± 1/16 inch

Typical Bushing Dimension References

