

Part No: 868SV-664

Schedule 80 PVC & CPVC

Clamp-On Saddle

Desc: 12X4 PVC CLAMP SADDLE D/O SOC FKM SS B

MSRP: 1136.38

Part Code: 086

Weight(lbs): 16.374

Weight(kg): 7.427

Weight(gm): 7427

Size: 12"X4"

Color: GRAY

Material: PVC

Connection Double Socket

Type Clamp Saddle

Hardware SS

O-Ring FKM



Hole Size = 4

No of Bolts = 6

H = 9-1/2

L = 8- 1/2

L1 = 14-1/4

M = 5- 1/4

N = 7/8

Bolt Torque = 10
FT./LBS.

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/32$ inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; $\pm 1/32$ inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/32$ inch

L = Overall length of fittings; $\pm 1/16$ inch.

M = Outside diameter of socket/thread hub; $\pm 1/16$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/16$ inch.

W = Height of cap; $\pm 1/16$ inch

Typical Molded Dimension References

