

Part No: 869-580SR

Schedule 80 PVC & CPVC

Clamp-On Saddle

Desc: 8X3 PVC CLAMP SADDLE D/O SRFPT EPDM ZN B

MSRP: 491.12

Part Code: 086

Weight(lbs): 11.18

Weight(kg): 5.071

Weight(gm): 5071

Size: 8"X3"

Color: GRAY

Material: PVC

Connection Double SR Fipt

Type Clamp Saddle

Hardware Zinc

O-Ring EPDM



H = 7-11/16

L = 8- 1/2

L1 = 10-1/16

M = 5- 1/4

N = 1-13/16

Hole Size = 4

Bolt = 10

No of = 6

Torque
FT./LBS.

Bolts

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; ± 1/32 inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; ± 1/32 inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; ± 1/32 inch

L = Overall length of fittings; ± 1/16 inch.

M = Outside diameter of socket/thread hub; ± 1/16 inch.

N = Socket bottom to socket bottom; couplings; ± 1/16 inch.

W = Height of cap; ± 1/16 inch

Typical Bushing Dimension References

