

Part No: 869-624SR

Schedule 80 PVC & CPVC

Clamp-On Saddle

Desc: 10X4 PVC CLAMP SADDLE D/O SRFPT EPDM ZN

MSRP: 619.67

Part Code: 086

Weight(lbs): 13.296

Weight(kg): 6.031

Weight(gm): 6031

Size: 10"X4"

Color: GRAY

Material: PVC

Connection Double SR Fipt

Type Clamp Saddle

Hardware Zinc

O-Ring EPDM



H = 8-7/16

L = 8- 1/2

L1 = 12-1/4

M = 5- 1/4

N = 1-17/32

Hole Size = 4

Bolt = 10

No of = 6

Torque
FT./LBS.

Bolts

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/32$ inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; $\pm 1/32$ inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/32$ inch

L = Overall length of fittings; $\pm 1/16$ inch.

M = Outside diameter of socket/thread hub; $\pm 1/16$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/16$ inch.

W = Height of cap; $\pm 1/16$ inch

Typical Molded Dimension References

