

Part No: 886-040GG

Nipples

Nipple

Desc: 1-1/2X4 PVC NIPPLE GROOVEXGROOVE SCH80

MSRP: 7.62

Part Code: 120

Weight(lbs): 0.234

Weight(kg): 0.106


Weight(gm): 106

Size: 1-1/2 X 4

Color: GRAY

Material: PVC

Nipple Type Groove X Groove



L = 4

L1 = 5/8

Fabricated Dimension References:

- G** = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/4$ & larger $\pm 1/2$ inch.
- H** = Intersection of center lines to face of fitting; 90° elbows, tees, crosses; $\pm 1/4$ inch.; wyes $\pm 1/2$ inch; 14" & larger inch.
- J** = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/4$ inch; 14" & larger $\pm 1/2$ inch.
- L** = Overall length of fittings; $\pm 1/2$ inch; wyes ± 1 inch; 14" & larger ± 1 inch.
- M** = Outside diameter of socket/thread hub; $\pm 1/4$ inch.
- N** = Socket bottom to socket bottom; couplings; $\pm 1/2$ inch.
- W** = Height of cap; $\pm 1/4$ inch.

Typical Fabricated Dimension References

