

Part No: 890-240P

Nipples

Nipple

Desc: 4X24 PVC NIPPLE PLAIN SCH80

MSRP: 146.03

Part Code: 120

Weight(lbs): 5.69

Weight(kg): 2.581

Weight(gm): 2581

Size: 4" x 24"

Color: GRAY

Material: PVC

Nipple Type Plain



L = 24

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/32$ inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; $\pm 1/32$ inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/32$ inch

L = Overall length of fittings; $\pm 1/16$ inch.

M = Outside diameter of socket/thread hub; $\pm 1/16$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/16$ inch.

W = Height of cap; $\pm 1/16$ inch

Typical Molded Dimension References

