

Part No: 899-002

Schedule 80 PVC & CPVC

Union

Desc: 1/4 PVC UNION SOCXFPT EPDM

MSRP: 40.96

Part Code: 080

Weight(lbs): 0.095

Weight(kg): 0.043

Weight(gm): 43


Size: 1/4"

Color: GRAY

Material: PVC

Connection Socket x Fipt

O-Ring EPDM



L = 1-15/16

M = 15/16

N = 3/4

NUT = 1-21/32
O.D.

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; ± 1/32 inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; ± 1/32 inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; ± 1/32 inch

L = Overall length of fittings; ± 1/16 inch.

M = Outside diameter of socket/thread hub; ± 1/16 inch.

N = Socket bottom to socket bottom; couplings; ± 1/16 inch.

W = Height of cap; ± 1/16 inch

Typical Molded Dimension References

