

Part No: 91122J850-005

All

AV-1

Desc: 1/2 CPVC TRUE UNION DIAPHRAGM VALVE, EPDM O-RINGS & DIAPHRAGM, SOC/THD W/ 90PSI AIR-TO-SPRING CLOSE LINEAR PNEUMATIC ACTUATOR, UNITIZED PLASTIC HOUSING

MSRP: 483.55

Part Code: 552

Weight(lbs): 2.509

Weight(kg): 1.138

Weight(gm): 1138

Size: 1/2

Color:

Material:

Connection EPDM O-ring and EPDM Diaphragm Socket

Under

Development

=

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/32$ inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; $\pm 1/32$ inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/32$ inch

L = Overall length of fittings; $\pm 1/16$ inch.

M = Outside diameter of socket/thread hub; $\pm 1/16$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/16$ inch.

W = Height of cap; $\pm 1/16$ inch

Typical Molded Dimension References

