

Part No: 91151A101-012

All

AV-1

Desc: 1 1/4 PVC TRUE UNION DIAPHRAGM VALVE, SOC, EPDM O-RINGS, PTFE/EPDM DIAPHRAGM W/ 115VAC MULTI-TURN ELECTRIC ACTUATOR, NEMA 4 ENCLOSURE, 25% DUTY CYCLE

MSRP: 3404.76

Part Code: 520

Weight(lbs): 13.633

Weight(kg): 6.184

Weight(gm): 6184

Size:

Color:

Material:

Connection EPDM O-ring and EPDM Backed PTFE Diaphragm

Under

Development

=

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/32$ inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; $\pm 1/32$ inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/32$ inch

L = Overall length of fittings; $\pm 1/16$ inch.

M = Outside diameter of socket/thread hub; $\pm 1/16$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/16$ inch.

W = Height of cap; $\pm 1/16$ inch

Typical Molded Dimension References

