

Part No: 91152H850-005

All

AV-1

Desc: 1/2 CPVC TRUE UNION DIAPHRAGM VALVE, PTFE/EPDM DIAPHRAGM, EPDM O-RINGS, S/T, W/ 90PSI AIR-TO-AIR LINEAR PNEUMATIC ACTUATOR, UNITIZED PLASTIC HOUSING

MSRP: 737.26

Part Code: 552

Weight(lbs): 1.865

Weight(kg): 0.846

Weight(gm): 846

Size: 1/2

Color:

Material:

Connection EPDM O-ring and EPDM Backed
PTFE Diaphragm Socket

Under

Development

=

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/32$ inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; $\pm 1/32$ inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/32$ inch

L = Overall length of fittings; $\pm 1/16$ inch.

M = Outside diameter of socket/thread hub; $\pm 1/16$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/16$ inch.

W = Height of cap; $\pm 1/16$ inch

Typical Molded Dimension References

