

Part No: 91251H850-010

All

AV-1

Desc: 1 PVC TRUE UNION DIAPHRAGM VALVE, PTFE/EPDM DIAPHRAGM, FKM O-RINGS, S/T, W/
90PSI AIR-TO-AIR LINEAR PNEUMATIC ACTUATOR, UNITIZED PLASTIC HOUSING

MSRP: 803.68

Part Code: 550

Weight(lbs): 2.657

Weight(kg): 1.205

Weight(gm): 1205

Size: 1

Color:

Material:

Connection FKM O-ring and EPDM Backed
PTFE Diaphragm Socket

Under

Development

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; ± 1/32 inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; ± 1/32 inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; ± 1/32 inch

L = Overall length of fittings; ± 1/16 inch.

M = Outside diameter of socket/thread hub; ± 1/16 inch.

N = Socket bottom to socket bottom; couplings; ± 1/16 inch.

W = Height of cap; ± 1/16 inch

Typical Molded Dimension References

