

Part No: 91252A101-010

All

AV-1

Desc: 1 CPVC TRUE UNION DIAPHRAGM VALVE, SOC, FKM O-RINGS, PTFE/EPDM DIAPHRAGM W/ 115VAC MULTI-TURN ELECTRIC ACTUATOR, NEMA 4 ENCLOSURE, 25% DUTY CYCLE

MSRP: 4748.19

Part Code: 522

Weight(lbs): 10.677

Weight(kg): 4.843

Weight(gm): 4843

Size:

Color:

Material:

Connection FKM O-ring and EPDM Backed
PTFE Diaphragm Socket

Under

Development

=

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/32$ inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; $\pm 1/32$ inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/32$ inch

L = Overall length of fittings; $\pm 1/16$ inch.

M = Outside diameter of socket/thread hub; $\pm 1/16$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/16$ inch.

W = Height of cap; $\pm 1/16$ inch

Typical Molded Dimension References

