

**Part No:** 93122H100-007

**All**

**AV-1**

**Desc:** 3/4 DIAPHRAGM VALVE CPVC SR THD EPDM WITH DOUBLE ACTING 80PSI AIR TO AIR LINEAR ACTUATOR WITH INDICATOR

**MSRP:** 3582.66

**Part Code:** 552

**Weight(lbs):** 5.498

**Weight(kg):** 2.494

**Weight(gm):** 2494

**Size:**

**Color:**

**Material:**

**Connection** EPDM O-ring and EPDM Diaphragm SR Thread

Under

Development

=

## Injection Molded Dimension References:

**G** = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses;  $\pm 1/32$  inch.

**H** = Intersection of center lines to face of fitting; 90° elbows tees, crosses;  $\pm 1/32$  inch.

**J** = Intersection of center lines to bottom of socket/thread; 45° elbows;  $\pm 1/32$  inch

**L** = Overall length of fittings;  $\pm 1/16$  inch.

**M** = Outside diameter of socket/thread hub;  $\pm 1/16$  inch.

**N** = Socket bottom to socket bottom; couplings;  $\pm 1/16$  inch.

**W** = Height of cap;  $\pm 1/16$  inch

## Typical Molded Dimension References

