

Part No: 94052H100-007

All

AV-1

Desc: 3/4 DIAPHRAGM VALVE CPVC SPG EPDM WITH EPDM/PTFE DPHGM 80PSI AIR TO AIR
LINEAR VARIABLE ACTUATOR WITH INDICATOR

MSRP: 3757.92

Part Code: 552

Weight(lbs): 5.176

Weight(kg): 2.348

Weight(gm): 2348

Size:

Color:

Material:

Connection EPDM O-ring and EPDM Backed
PTFE Diaphragm Spigot

Under

Development

=

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/32$ inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; $\pm 1/32$ inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/32$ inch

L = Overall length of fittings; $\pm 1/16$ inch.

M = Outside diameter of socket/thread hub; $\pm 1/16$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/16$ inch.

W = Height of cap; $\pm 1/16$ inch

Typical Molded Dimension References



The information printed here is based on current information & product design at the time of publication and is subject to change without notification. Spears® ongoing commitment to product improvement may result in some variation. No representation, guarantees or warranties of any kind are as to its accuracy, suitability for particular application or results to be obtained therefrom. For verification of technical data or additional information, please contact Spears® Technical Service Department :: WEST COAST : (818) 364-1611 - EAST COAST : (717) 938-9006