

**Part No:** 95021A101-025

**All**

**AV-1**

**Desc:** 2-1/2 PVC DIAPHRAGM VALVE FLANGED EPDM DIAPHRAGM W/ 115VAC MULTI-TURN ELECTRIC ACTUATOR, NEMA 4 ENCLOSURE, 25% DUTY CYCLE

**MSRP:** 5784.69

**Part Code:** 520

**Weight(lbs):** 89.058

**Weight(kg):** 40.396

**Weight(gm):** 40396

**Size:** 2-1/2

**Color:**

**Material:**

**Connection** EPDM O-ring EPDM Diphragm  
Flanged

Under

Development

=

## Injection Molded Dimension References:

**G** = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses;  $\pm 1/32$  inch.

**H** = Intersection of center lines to face of fitting; 90° elbows tees, crosses;  $\pm 1/32$  inch.

**J** = Intersection of center lines to bottom of socket/thread; 45° elbows;  $\pm 1/32$  inch

**L** = Overall length of fittings;  $\pm 1/16$  inch.

**M** = Outside diameter of socket/thread hub;  $\pm 1/16$  inch.

**N** = Socket bottom to socket bottom; couplings;  $\pm 1/16$  inch.

**W** = Height of cap;  $\pm 1/16$  inch

## Typical Molded Dimension References

