

Part No: 95052H100-007

All

AV-1

Desc: 3/4 DIAPHRAGM VALVE CPVC FLG EPDM WITH EPDM/PTFE DPHGM 80PSI AIR TO AIR
LINEAR ACTUATOR WITH INDICATOR

MSRP: 3108.01

Part Code: 552

Weight(lbs): 5.732

Weight(kg): 2.6

Weight(gm): 2600

Size:

Color:

Material:

Connection EPDM O-ring and EPDM Backed
PTFE Diaphragm Flanged

Under

Development

=

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/32$ inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; $\pm 1/32$ inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/32$ inch

L = Overall length of fittings; $\pm 1/16$ inch.

M = Outside diameter of socket/thread hub; $\pm 1/16$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/16$ inch.

W = Height of cap; $\pm 1/16$ inch

Typical Molded Dimension References

