

Part No: 95053H100-040

All

AV-1

Desc: 4 DIAPHRAGM VALVE PP FLG EPDM WITH EPDM/PTFE DPHGM 80PSI AIR TO AIR LINEAR ACTUATOR WITH INDICATOR

MSRP: 6413.21

Part Code: 554

Weight(lbs): 121.256

Weight(kg): 55.001

Weight(gm): 55001

Size:

Color:

Material:

Connection EPDM O-ring and EPDM Backed
PTFE Diaphragm Flanged

Under

Development

=

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/32$ inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; $\pm 1/32$ inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/32$ inch

L = Overall length of fittings; $\pm 1/16$ inch.

M = Outside diameter of socket/thread hub; $\pm 1/16$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/16$ inch.

W = Height of cap; $\pm 1/16$ inch

Typical Molded Dimension References

