

Part No: A-DSV15

All

AV-1

Desc: 24VDC 4-WAY SOLENOID VALVE, NEMA 4/4X ENCLOSURE

MSRP: 2800.34

Part Code: 298

Weight(lbs): 4.504

Weight(kg): 2.043

Weight(gm): 2043

Size: 24 VDC

Color:

Material:

Under

Development

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/32$ inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; $\pm 1/32$ inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/32$ inch

L = Overall length of fittings; $\pm 1/16$ inch.

M = Outside diameter of socket/thread hub; $\pm 1/16$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/16$ inch.

W = Height of cap; $\pm 1/16$ inch

Typical Molded Dimension References

