

Part No: BS22P6-030

Filters & Strainers

Basket Strainers

Desc: 3 PVC BASKET STRAINER SOC EPDM P6 MESH

MSRP: 2889.52

Part Code: 295

Weight(lbs): 23.964


Weight(kg): 10.87

Weight(gm): 10870

Size: 3"

Color: GRAY

Material: PVC



H = 14-1/4

H1 = 9-1/8

L = 22-7/8

L2 = 16-1/8

N = 11-5/8

Cv = 172

Values

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; ± 1/32 inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; ± 1/32 inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; ± 1/32 inch

L = Overall length of fittings; ± 1/16 inch.

M = Outside diameter of socket/thread hub; ± 1/16 inch.

N = Socket bottom to socket bottom; couplings; ± 1/16 inch.

W = Height of cap; ± 1/16 inch

Typical Molded Dimension References

