

Part No: BS27P6-100

Filters & Strainers

Basket Strainers

Desc: 10 PVC BASKET STRAINER SPG EPDM P6 MESH

MSRP: 13954.13

Part Code: 295

Weight(lbs): 134.416


Weight(kg): 60.97

Weight(gm): 60970

Size: 10"

Color: GRAY

Material: PVC



Connection Spigot

O-Ring EPDM

Mesh Sieve # 6 = (1/8")

H = 27- 1/8

H1 = 16- 5/8

Cv = 893
Values

L = 43-3/4

L3 = 34- 1/2

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; ± 1/32 inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; ± 1/32 inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; ± 1/32 inch

L = Overall length of fittings; ± 1/16 inch.

M = Outside diameter of socket/thread hub; ± 1/16 inch.

N = Socket bottom to socket bottom; couplings; ± 1/16 inch.

W = Height of cap; ± 1/16 inch

Typical Molded Dimension References

