

Part No: BS32P6-060

Filters & Strainers

Basket Strainers

Desc: 6 PVC BASKET STRAINER SOC FKM P6 MESH

MSRP: 6138.32

Part Code: 295

Weight(lbs): 62.479


Weight(kg): 28.34

Weight(gm): 28340

Size: 6"

Color: GRAY

Material: PVC



H = 18- 7/8

H1 = 11- 9/16

L = 30- 7/16

L2 = 24- 3/8

N = 17- 7/8

Cv = 630

Values

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; ± 1/32 inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; ± 1/32 inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; ± 1/32 inch

L = Overall length of fittings; ± 1/16 inch.

M = Outside diameter of socket/thread hub; ± 1/16 inch.

N = Socket bottom to socket bottom; couplings; ± 1/16 inch.

W = Height of cap; ± 1/16 inch

Typical Molded Dimension References

