

Part No: BS32P6-100

Filters & Strainers

Basket Strainers

Desc: 10 PVC BASKET STRAINER SOC FKM P6 MESH

MSRP: 15260.73

Part Code: 295

Weight(lbs): 136.162


Weight(kg): 61.762

Weight(gm): 61762

Size: 10"

Color: GRAY

Material: PVC



Connection Socket

O-Ring FKM

Mesh Sieve # 6 = (1/8")

H = 27- 1/8

H1 = 16- 5/8

L = 43-3/4

L2 = 34- 9/16

N = 24- 1/16

Cv = 893

Values

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; ± 1/32 inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; ± 1/32 inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; ± 1/32 inch

L = Overall length of fittings; ± 1/16 inch.

M = Outside diameter of socket/thread hub; ± 1/16 inch.

N = Socket bottom to socket bottom; couplings; ± 1/16 inch.

W = Height of cap; ± 1/16 inch

Typical Molded Dimension References

