

Part No: BS37P6-080

Filters & Strainers

Basket Strainers

Desc: 8 PVC BASKET STRAINER SPG FKM P6 MESH

MSRP: 8183.29

Part Code: 295

Weight(lbs): 96.245

Weight(kg): 43.656

Weight(gm): 43656

Size: 8"


Color: GRAY

Material: PVC

Connection Spigot

O-Ring FKM

Mesh Sieve # 6 = (1/8")



H = 24- 1/2

H1 = 12- 9/16

L = 37- 1/16

L3 = 27- 1/2

Cv = 750
Values

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; ± 1/32 inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; ± 1/32 inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; ± 1/32 inch

L = Overall length of fittings; ± 1/16 inch.

M = Outside diameter of socket/thread hub; ± 1/16 inch.

N = Socket bottom to socket bottom; couplings; ± 1/16 inch.

W = Height of cap; ± 1/16 inch

Typical Molded Dimension References

