

Part No: BS37S6-020C

Filters & Strainers

Basket Strainers

Desc: 2 CPVC BASKET STRAINER SPG FKM S6 MESH

MSRP: 2872.84

Part Code: 297

Weight(lbs): 12.632

Weight(kg): 5.73

Weight(gm): 5730

Size: 2"


Color: GRAY

Material: CPVC

Connection Spigot

O-Ring FKM

Mesh Sieve # 6 = (1/8")



H = 10- 1/4

H1 = 7- 7/8

L = 18- 1/8

L3 = 11

Cv = 72
Values

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; ± 1/32 inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; ± 1/32 inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; ± 1/32 inch

L = Overall length of fittings; ± 1/16 inch.

M = Outside diameter of socket/thread hub; ± 1/16 inch.

N = Socket bottom to socket bottom; couplings; ± 1/16 inch.

W = Height of cap; ± 1/16 inch

Typical Molded Dimension References

