

Part No: E1454-007

All

AV-1

Desc: 3/4 PVC TRUE UNION 2000 STANDARD BALL VALVE SOC/THD FKM W/ 115VAC UNIDIRECTIONAL ACTUATOR, 25% DUTY CYCLE, NEMA 4X ENCLOSURE W/ POSITION INDICATOR

MSRP: 635.46

Part Code: 500

Weight(lbs): 3.274

Weight(kg): 1.485

Weight(gm): 1485

Size: 3/4

Color:

Material:

Connection FKM Socket

Under

Development

=

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/32$ inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; $\pm 1/32$ inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/32$ inch

L = Overall length of fittings; $\pm 1/16$ inch.

M = Outside diameter of socket/thread hub; $\pm 1/16$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/16$ inch.

W = Height of cap; $\pm 1/16$ inch

Typical Molded Dimension References

