

**Part No:** FLR-200-1

**All**

**FILTERS-1**

**Desc:** 200 FINE MESH SS SCREEN OUTSIDE REV FLOW

**MSRP:** 839.07

**Part Code:** 020

**Weight(lbs):** 1.967

**Weight(kg):** 0.892

**Weight(gm):** 892

**Size:**

**Color:**

**Material:**

# Under

# Development

## Injection Molded Dimension References:

**G** = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses;  $\pm 1/32$  inch.

**H** = Intersection of center lines to face of fitting; 90° elbows tees, crosses;  $\pm 1/32$  inch.

**J** = Intersection of center lines to bottom of socket/thread; 45° elbows;  $\pm 1/32$  inch

**L** = Overall length of fittings;  $\pm 1/16$  inch.

**M** = Outside diameter of socket/thread hub;  $\pm 1/16$  inch.

**N** = Socket bottom to socket bottom; couplings;  $\pm 1/16$  inch.

**W** = Height of cap;  $\pm 1/16$  inch

## Typical Molded Dimension References

