

Part No: HT2S-524

Schedule 80 PVC & CPVC

Hot-Tap Saddle

Desc: 6X3/4 PVC HOT TAP SADDLE EPDM S/S BOLT

MSRP: 212.44

Part Code: 049

Weight(lbs): 2.535

Weight(kg): 1.15

Weight(gm): 1150

Size: 6"X 3/4"SOC(1"SPG)

Color: GRAY

Material: PVC



L = 3

G = 6

G1 = 1

H = 8-5/8

H1 = 2

H2 = 3-13/16

M = 2

L1 = 8-3/16

Connection Saddle x Socket (Spigot)

Hardware SS316

O-Ring EPDM

NOTE Not intended To Convey Or
Dispense Water For Human
Consumption Through Drinking
Or Cooking

Cutter Brass

Type Hot-Tap

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/32$ inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; $\pm 1/32$ inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/32$ inch

L = Overall length of fittings; $\pm 1/16$ inch.

M = Outside diameter of socket/thread hub; $\pm 1/16$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/16$ inch.

W = Height of cap; $\pm 1/16$ inch

Typical Molded Dimension References

