

**Part No:** HT3-416C

**Schedule 80 PVC & CPVC**

**Hot-Tap Saddle**

**Desc:** 4X3/4 CPVC HOT TAP CLAMP SDLE FKM ZN BLT

**MSRP:** 341.37

**Part Code:** 050

**Weight(lbs):** 1.773

**Weight(kg):** 0.804

**Weight(gm):** 804

**Size:** 4"X 3/4" SOC(1"SPG)

**Color:** GRAY

**Material:** CPVC



**L** = 3

**G** = 4-11/16

**G1** = 1

**H** = 7-5/16

**H1** = 2

**H2** = 2-5/8

**M** = 2

**L1** = 5-13/16

**Connection** Saddle x Socket (Spigot)

**Hardware** Zinc Plated

**O-Ring** FKM

**NOTE** Not intended To Convey Or  
Dispense Water For Human  
Consumption Through Drinking  
Or Cooking

**Cutter** Brass

**Type** Hot-Tap

## Injection Molded Dimension References:

**G** = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; ± 1/32 inch.

**H** = Intersection of center lines to face of fitting; 90° elbows tees, crosses; ± 1/32 inch.

**J** = Intersection of center lines to bottom of socket/thread; 45° elbows; ± 1/32 inch

**L** = Overall length of fittings; ± 1/16 inch.

**M** = Outside diameter of socket/thread hub; ± 1/16 inch.

**N** = Socket bottom to socket bottom; couplings; ± 1/16 inch.

**W** = Height of cap; ± 1/16 inch

## Typical Molded Dimension References

