

Part No: HT3S-251

Schedule 80 PVC & CPVC

Hot-Tap Saddle

Desc: 2X1-1/2 PVC HOT TAP SADDLE FKM S/S BOLT

MSRP: 299.89

Part Code: 049

Weight(lbs): 2.189

Weight(kg): 0.993

Weight(gm): 993

Size: 2"X1-1/2"SOC(2"SPG)

Color: GRAY

Material: PVC



L = 2-7/16

G = 4-1/2

G1 = 1-1/4

H = 8-1/2

H1 = 2-11/16

H2 = 1-1/2

M = 2-7/8

L1 = 3-7/16

Connection Saddle x Socket (Spigot)

Hardware SS316

O-Ring FKM

NOTE Not intended To Convey Or
Dispense Water For Human
Consumption Through Drinking
Or Cooking

Cutter Brass

Type Hot-Tap

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/32$ inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; $\pm 1/32$ inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/32$ inch

L = Overall length of fittings; $\pm 1/16$ inch.

M = Outside diameter of socket/thread hub; $\pm 1/16$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/16$ inch.

W = Height of cap; $\pm 1/16$ inch

Typical Molded Dimension References

