

Part No: LF1002

Lab Specialty

Lab Fixture

Desc: PVCLAB FIXT DECK-MNT BALL VLV EPDM

MSRP: 175.16

Part Code: 218

Weight(lbs): 0.578


Weight(kg): 0.262

Weight(gm): 262

Size:

Color: GRAY

Material: PVC



Type Deck Mount Lab Fixture W/Valve
-Direct Flow

Connection Fixture

O-Ring EPDM

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/32$ inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; $\pm 1/32$ inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/32$ inch

L = Overall length of fittings; $\pm 1/16$ inch.

M = Outside diameter of socket/thread hub; $\pm 1/16$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/16$ inch.

W = Height of cap; $\pm 1/16$ inch

Typical Molded Dimension References

