

Part No: MTF3-100C

Filters & Strainers

Irrigation Filters

Desc: 50 GPM CPVC IND T-FILTER 100 MESH SS FKM

MSRP: 1570.07

Part Code: 296

Weight(lbs): 8.486

Weight(kg): 3.849

Weight(gm): 3849

Size: 50 GPM

Color: GRAY

Material: CPVC

Connection FKM O-ring Seal with Stainless Steel Screen

Under

Development

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/32$ inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; $\pm 1/32$ inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/32$ inch

L = Overall length of fittings; $\pm 1/16$ inch.

M = Outside diameter of socket/thread hub; $\pm 1/16$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/16$ inch.

W = Height of cap; $\pm 1/16$ inch

Typical Molded Dimension References

