

Part No: P700-080C

LabWaste®

Bend/Ell

Desc: 8 CPVC DWV RETURN BEND HUBXHUB

MSRP: 733.6

Part Code: 159

Weight(lbs): 20.812

Weight(kg): 9.44

Weight(gm): 9440


Size: 8

Color: GRAY

Material: CPVC

Type Return Bend

Connection Hub x Hub



G = 6

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/32$ inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; $\pm 1/32$ inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/32$ inch

L = Overall length of fittings; $\pm 1/16$ inch.

M = Outside diameter of socket/thread hub; $\pm 1/16$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/16$ inch.

W = Height of cap; $\pm 1/16$ inch

Typical Molded Dimension References

