

**Part No:** S110-07

**All**

**DCVRF-1**

**Desc:** 3/4 PVC COMPRESSION COUPLING

**MSRP:** 8.76

**Part Code:** 024

**Weight(lbs):** 0.289

**Weight(kg):** 0.131

**Weight(gm):** 131

**Size:** 3/4"

**Color:**

**Material:**

**Connection** Buna-N Gasket

# Under

# Development

**N** = 3-9/16

**M** = 2-1/8

**L** = 5-7/16

## Injection Molded Dimension References:

**G** = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; ± 1/32 inch.

**H** = Intersection of center lines to face of fitting; 90° elbows tees, crosses; ± 1/32 inch.

**J** = Intersection of center lines to bottom of socket/thread; 45° elbows; ± 1/32 inch

**L** = Overall length of fittings; ± 1/16 inch.

**M** = Outside diameter of socket/thread hub; ± 1/16 inch.

**N** = Socket bottom to socket bottom; couplings; ± 1/16 inch.

**W** = Height of cap; ± 1/16 inch

## Typical Molded Dimension References

