



Actuated Valves
Pneumatic Actuator Accessories for Ball Valves & Butterfly Valves

Accessory	Description	Accessory Part Number	Price Each Disc Code: 298
ID Tag	Type 316 Stainless Steel ID Tag 1/2" x 3" (3-lines, 12-characters & spaces)	TAG3-015	30.03
Stem Extensions	Ball Valve Stem Extension ²	A-BVSE-xxx-000	Call for pricing
	True Union 2000 Ball Valve Stem Extension ²	A-BVSE2-xxx-000	
	Butterfly Valve Stem Extension ²	A-BFSE-xxx-000	

NOTES: 1 - Pneumatic and Electro-Pneumatic positioners include brass gauges: 1 input gauge @ 0-30 psi and 2 output gauges @ 0-160 psi. Stainless steel gauges may be ordered separately.
 2 - Stem Extension Part Numbers: Enter size code for "xxx" in part number. Replace "000" with desired length code in part number; length is from top of valve to bottom of actuator.

**Actuated Valves
Pneumatic Actuator Accessories for Diaphragm Valves**



The following accessories are for use on Spears® pneumatic actuated Diaphragm Valves only. See separate listing for Ball Valve and Butterfly Valve pneumatic accessories. Accessories are individually ordered separately and factory assembled with the selected Premium Actuated Valve Package. See important ordering instructions, *Ordering Premium Valve Packages with Accessory Add-ons*.

Accessory	Description	Accessory Part Number	Price Each Disc Code: 298
Pneumatic Positioners	3-15 psi NEMA 4x w/ Visual Indicator Top Loading (no gauge)	A-DPP1	4350.17
	3-15 psi NEMA 4x w/ Visual Indicator Top Loading w/ gauges (3)	A-DPP2	4924.35
	3-15 psi NEMA 4x w/ Visual Indicator Bottom Loading (no gauge)	A-DPP3	4350.18
	3-15 psi NEMA 4x w/ Visual Indicator Bottom Loading w/ gauges (3)	A-DPP4	4924.35
Electro Pneumatic Positioners	4-20mA (3-15 psi) NEMA 4x w/Visual Indicator (up to 2")	A-DEP1	8325.69
	4-20mA (3-15 psi) NEMA 4x w/Visual Indicator w/SS Gauges (up to 2")	A-DEP2	8899.87
	4-20mA (3-15 psi) NEMA 4x w/Visual Indicator (2-1/2" & up)	A-DEP3	8325.69
	4-20mA (3-15 psi) NEMA 4x w/Visual Indicator w/SS Gauges (2-1/2" & up)	A-DEP4	8899.87
3-Way Solenoid Valves	115 VAC NEMA 4/4x	A-DSV1	358.19
	230 VAC NEMA 4/4x	A-DSV2	358.19
	24 VAC NEMA 4/4x	A-DSV3	358.19
	12 VDC NEMA 4/4x	A-DSV4	358.19
	24 VDC NEMA 4/4x	A-DSV5	358.19
	115 VAC NEMA 4/4x/7/9	A-DSV6	552.86
	230 VAC NEMA 4/4x/7/9	A-DSV7	552.86
	24 VAC NEMA 4/4x/7/9	A-DSV8	552.86
	12 VDC NEMA 4/4x/7/9	A-DSV9	552.86
	24 VDC NEMA 4/4x/7/9	A-DSV10	552.86
4-Way Solenoid Valves	115 VAC NEMA 4/4x	A-DSV11	669.57
	230 VAC NEMA 4/4x	A-DSV12	669.57
	24 VAC NEMA 4/4x	A-DSV13	669.57
	12 VDC NEMA 4/4x	A-DSV14	669.57
	24 VDC NEMA 4/4x	A-DSV15	669.57
	115 VAC NEMA 4/4x/7/9	A-DSV16	938.43
	230 VAC NEMA 4/4x/7/9	A-DSV17	938.43
	24 VAC NEMA 4/4x/7/9	A-DSV18	938.43
	12 VDC NEMA 4/4x/7/9	A-DSV19	938.43
	24 VDC NEMA 4/4x/7/9	A-DSV20	938.43
Micro Limit Switches	2-SPDT NEMA 4 w/ 180° Visual Indicator ¹	A-DLS20	1083.29
	2-SPDT NEMA 7/9 w/ 180° Visual Indicator ¹	A-DLS25	1931.66
Proximity Limit Switches	2-SPDT NEMA 4/4X	A-DLS23	1748.64
Limit Switches	2-SPDT NEMA 4 ²	A-DLS24	1260.78
Speed Controller	Variable Speed Controller	A-DPSC1	1085.18
ID Tag	Type 316 Stainless Steel ID Tag 1/2" x 3" (3-lines, 12-characters & spaces)	TAG3-015	30.03

Stem Extensions	Diaphragm Valve Stem Extension ³	A-DPSE-xxx-000	Call for pricing
------------------------	---	----------------	------------------

- NOTES: 1 - Micro Limit Switches used on valve sizes ½" through 2".
 2 - Limit Switches used on valve sizes 2-1/2" & larger
 3 - Stem Extension Part Numbers: Enter size code for "xxx" in part number. Replace "000" with desired length code in part number; length is from top of valve to bottom of actuator.



**Actuated Valves
Electric Actuator Accessories**

Contact Spears® for any desired accessories or functions not specified in the Accessory Selection Tables

The following accessories are for use on Spears® electric actuated Ball Valves, Butterfly Valves and Diaphragm Valves. Accessories are individually ordered separately and factory assembled with the selected Premium Actuated Valve Package. See important ordering instructions, *Ordering Premium Valve Packages with Accessory Add-ons*.

Accessory	Description	Accessory Part Number	Price Each Disc Code: 298
Heater	Heater/Thermostat - On 41°F, Off 60.8°F	A-H1	195.33
	Heater/Thermostat - On 62.6°F, Off 80.6°F	A-H2	175.78
Auxiliary Limit Switches	2-SPDT Limit Switch Set (1/2" shaft cam) ¹	A-LS1	175.22
	2-SPDT Limit Switch Set (3/8" shaft cam) ¹	A-LS2	175.22
	2-SPDT Limit Switch Set for Electric Spring Return	A-LS3	157.20
Position Indicators	LED Indicator Lights	A-P2	223.84
Modulating Positioner Boards	115 VAC 4-20 mA	A-PB1	1790.66
	115 VAC 0-5 VDC	A-PB2	1790.66
	115 VAC 0-10 VDC	A-PB3	1790.66
	230 VAC 4-20 mA	A-PB4	1790.66
	230 VAC 0-5 VDC	A-PB5	1790.66
	230 VAC 0-10 VDC	A-PB6	1790.66
	24 VAC 4-20 mA	A-PB7	1790.66
	24 VAC 0-5 VDC	A-PB8	1790.66
	24 VAC 0-10 VDC	A-PB9	1790.66
	24 VDC 4-20 mA	A-PB10	1790.66
	24 VDC 0-5 VDC	A-PB11	1790.66
	24 VDC 0-10 VDC	A-PB12	1790.66
	115 VAC 4-20 mA For Electric Spring Return Actuator	A-PB13	1871.64
Transmitter	4-20mA	A-T1	1313.85
Torque Sensors	Adjustable Electronic Torque Sensor	A-TS1	948.86
Speed Controller	Variable Speed Controller	A-SC1	623.10
"2-Wire" Control (operates as solenoid valve)	Control Relay Switch Setup 115 VAC- Normally Closed ²	A-CR1	221.40
	Control Relay Switch Setup 115 VAC- Normally Open ²	A-CR2	221.40
	Control Relay Switch Setup 24 VAC- Normally Closed ²	A-CR3	221.40
	Control Relay Switch Setup 24 VAC- Normally Open ²	A-CR4	221.40
	Control Relay Switch Setup 230 VAC- Normally Closed ²	A-CR5	221.40
	Control Relay Switch Setup 230 VAC- Normally Open ²	A-CR6	221.40
	Control Relay Switch Setup 12 VDC- Normally Closed ²	A-CR7	221.40
	Control Relay Switch Setup 12 VDC- Normally Open ²	A-CR8	221.40
	Control Relay Switch Setup 24 VDC- Normally Closed ²	A-CR9	221.40
	Control Relay Switch Setup 24 VDC- Normally Open ²	A-CR10	221.40
Friction Brake	Mechanical Brake ³	A-FB1	367.85
Lockout Switch	Power disconnect switch activated when manual override is in use	A-LK1	255.32
ID Tag	Type 316 Stainless Steel ID Tag 1/2" x 3" (3-lines, 12-characters & spaces)	TAG3-015	30.03

Stem Extensions	Ball Valve Stem Extension ⁴	A-BVSE-xxx-000	Call for pricing
	True Union 2000 Ball Valve Stem Extension ⁴	A-BVSE2-xxx-000	
	Butterfly Valve Stem Extension ⁴	A-BFSE-xxx-000	
	Diaphragm Valve Stem Extension ⁴	A-DESE-xxx-000	

- NOTES: 1 - The A-LS2 is used on 1/2" - 2" basic Ball Valve packages; A-LS1 used on all other sizes.
 2 - "2-Wire" Control is not applicable to Diaphragm Valves.
 3 - Friction Brake is standard on Butterfly Valves and not applicable to Diaphragm Valves.
 4 - Stem Extension Part Numbers: Enter size code for "xxx" in part number. Replace "000" with desired length code in part number; length is from top of valve to bottom of actuator.