

**Part No:** TF3-100

**All**

**STRAINER&FILTER**

**Desc:** 100 GPM PVC IND T-FILTER 100 MESH SS FKM

**MSRP:** 1657.98

**Part Code:** 295

**Weight(lbs):** 10.922

**Weight(kg):** 4.954

**Weight(gm):** 4954

**Size:** 100 GPM

**Color:**

**Material:**

**Connection** FKM O-ring Seal with Stainless Steel Screen

Under

Development

## Injection Molded Dimension References:

**G** = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses;  $\pm 1/32$  inch.

**H** = Intersection of center lines to face of fitting; 90° elbows tees, crosses;  $\pm 1/32$  inch.

**J** = Intersection of center lines to bottom of socket/thread; 45° elbows;  $\pm 1/32$  inch

**L** = Overall length of fittings;  $\pm 1/16$  inch.

**M** = Outside diameter of socket/thread hub;  $\pm 1/16$  inch.

**N** = Socket bottom to socket bottom; couplings;  $\pm 1/16$  inch.

**W** = Height of cap;  $\pm 1/16$  inch

## Typical Molded Dimension References

