

Part No: TF3-200

All

STRAINER&FILTER

Desc: 100 GPM PVC IND T-FILTER 200 MESH SS FKM

MSRP: 1865.51

Part Code: 295

Weight(lbs): 10.953

Weight(kg): 4.968

Weight(gm): 4968

Size: 100 GPM

Color:

Material:

Connection FKM O-ring Seal with Stainless Steel Screen

Under

Development

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/32$ inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; $\pm 1/32$ inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/32$ inch

L = Overall length of fittings; $\pm 1/16$ inch.

M = Outside diameter of socket/thread hub; $\pm 1/16$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/16$ inch.

W = Height of cap; $\pm 1/16$ inch

Typical Molded Dimension References

