

Part No: TFR3-150

All

STRAINER&FILTER

Desc: 100 GPM REVFLO IND T-FLTR 150 MSH SS FKM

MSRP: 1717.22

Part Code: 295

Weight(lbs): 11.44

Weight(kg): 5.189

Weight(gm): 5189

Size: 100 GPM

Color:

Material:

Connection FKM O-ring Seal with Stainless Steel Screen

Under

Development

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/32$ inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; $\pm 1/32$ inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/32$ inch

L = Overall length of fittings; $\pm 1/16$ inch.

M = Outside diameter of socket/thread hub; $\pm 1/16$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/16$ inch.

W = Height of cap; $\pm 1/16$ inch

Typical Molded Dimension References

