

Part No: TUMB-015

All

BV-1

Desc: 1-1/2 PP T/U REG B/V MULTI-MOUNT BRACKET

MSRP: 212.46

Part Code: 298

Weight(lbs): 0.902

Weight(kg): 0.409

Weight(gm): 409

Size: 1-1/2

Color:

Material:

Connection Regular True Union

Under

Development

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/32$ inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; $\pm 1/32$ inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/32$ inch

L = Overall length of fittings; $\pm 1/16$ inch.

M = Outside diameter of socket/thread hub; $\pm 1/16$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/16$ inch.

W = Height of cap; $\pm 1/16$ inch

Typical Molded Dimension References

