

Part No: YS21S8-012CLSR

Filters & Strainers

Y-Strainers

Desc: 1-1/4 PVC CL Y STRAINER SR/FPT EPDM SS8M

MSRP: 593.6

Part Code: 103

Weight(lbs): 1.501

Weight(kg): 0.681

Weight(gm): 681

Size: 1-1/4"

Color: CLEAR

Material: PVC

Connection SR Fipt

O-Ring EPDM

Mesh Sieve # 8

Body Color Clear



A = 5- 5/16

A1 = 8- 3/8

B = 6

C = 7-15/16

D = 4- 1/4

E = 2-13/16

Cv = 33.6
Values

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; ± 1/32 inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; ± 1/32 inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; ± 1/32 inch

L = Overall length of fittings; ± 1/16 inch.

M = Outside diameter of socket/thread hub; ± 1/16 inch.

N = Socket bottom to socket bottom; couplings; ± 1/16 inch.

W = Height of cap; ± 1/16 inch

Typical Molded Dimension References

