



Strainers & Filters Y-Strainers & True Union Y-Strainers

PVC Clear - Flanged Ends (continued)

Size	EPDM Seals PVC Screen	EPDM Seals SS Screen	Viton® Seals PVC Screen	Viton® Seals SS Screen	Std Pk	Mstr Pk	Disc Code
1-1/2	YS23P8-015CL 273.89	YS23S8-015CL 457.01	YS33P8-015CL 304.12	YS33S8-015CL 616.53	1	4	103
2	YS23P8-020CL 344.35	YS23S8-020CL 544.33	YS33P8-020CL 377.84	YS33S8-020CL 700.41	1	0	103
3	YS23P8-030CL 760.63	YS23S8-030CL 933.55	YS33P8-030CL 817.23	YS33S8-030CL 990.64	1	0	103
4	YS23P8-040CL 1225.87	YS23S8-040CL 1443.20	YS33P8-040CL 1317.70	YS33S8-040CL 1535.00	1	0	103

CPVC - Socket Ends

Size	EPDM Seals CPVC Screen	EPDM Seals SS Screen	Viton® Seals CPVC Screen	Viton® Seals SS Screen	Std Pk	Mstr Pk	Disc Code
1/2	YS22C8-005C 220.59	YS22S8-005C 303.17	YS32C8-005C 247.02	YS32S8-005C 340.78	1	18	104
3/4	YS22C8-007C 242.37	YS22S8-007C 344.78	YS32C8-007C 272.87	YS32S8-007C 387.53	1	18	104
1	YS22C8-010C 307.98	YS22S8-010C 426.45	YS32C8-010C 346.91	YS32S8-010C 478.56	1	12	104
1-1/4	YS22C8-012C 447.09	YS22S8-012C 615.30	YS32C8-012C 538.04	YS32S8-012C 651.54	1	8	104
1-1/2	YS22C8-015C 480.24	YS22S8-015C 635.59	YS32C8-015C 558.20	YS32S8-015C 710.62	1	8	104
2	YS22C8-020C 679.96	YS22S8-020C 796.78	YS32C8-020C 718.49	YS32S8-020C 869.04	1	4	104
3	YS22C8-030C 811.12	YS22S8-030C 970.28	YS32C8-030C 855.51	YS32S8-030C 1043.76	1	0	104
4	YS22C8-040C 1404.94	YS22S8-040C 1606.94	YS32C8-040C 1510.53	YS32S8-040C 1727.84	1	0	104

CPVC - SR Threaded Ends

Size	EPDM Seals CPVC Screen	EPDM Seals SS Screen	Viton® Seals CPVC Screen	Viton® Seals SS Screen	Std Pk	Mstr Pk	Disc Code
1/2	YS21C8-005CSR 228.62	YS21S8-005CSR 311.20	YS31C8-005CSR 255.06	YS31S8-005CSR 348.82	1	18	104
3/4	YS21C8-007CSR 250.97	YS21S8-007CSR 353.36	YS31C8-007CSR 281.46	YS31S8-007CSR 396.13	1	12	104
1	YS21C8-010CSR 327.67	YS21S8-010CSR 446.11	YS31C8-010CSR 366.61	YS31S8-010CSR 498.21	1	8	104
1-1/4	YS21C8-012CSR 467.31	YS21S8-012CSR 600.88	YS31C8-012CSR 558.27	YS31S8-012CSR 671.79	1	8	104
1-1/2	YS21C8-015CSR 503.66	YS21S8-015CSR 659.00	YS31C8-015CSR 634.34	YS31S8-015CSR 734.02	1	4	104
2	YS21C8-020CSR 713.31	YS21S8-020CSR 830.13	YS31C8-020CSR 799.53	YS31S8-020CSR 902.36	1	0	104
3	YS21C8-030CSR 852.44	YS21S8-030CSR 1011.61	YS31C8-030CSR 912.14	YS31S8-030CSR 1085.07	1	0	104
4	YS21C8-040CSR 1447.78	YS21S8-040CSR 1649.81	YS31C8-040CSR 1553.38	YS31S8-040CSR 1770.71	1	0	104

CPVC - Flanged Ends

Size	EPDM Seals CPVC Screen	EPDM Seals SS Screen	Viton® Seals CPVC Screen	Viton® Seals SS Screen	Std Pk	Mstr Pk	Disc Code
1/2	YS23C8-005C 355.72	YS23S8-005C 436.73	YS33C8-005C 394.83	YS33S8-005C 487.23	1	8	104
3/4	YS23C8-007C 377.84	YS23S8-007C 464.59	YS33C8-007C 409.73	YS33S8-007C 518.49	1	8	104
1	YS23C8-010C 403.47	YS23S8-010C 516.20	YS33C8-010C 439.53	YS33S8-010C 575.49	1	8	104
1-1/4	YS23C8-012C 646.77	YS23S8-012C 796.18	YS33C8-012C 705.09	YS33S8-012C 886.56	1	4	104
1-1/2	YS23C8-015C 720.76	YS23S8-015C 884.65	YS33C8-015C 800.28	YS33S8-015C 986.94	1	4	104
2	YS23C8-020C 906.18	YS23S8-020C 1106.13	YS33C8-020C 994.34	YS33S8-020C 1157.39	1	0	104
3	YS23C8-030C 1238.11	YS23S8-030C 1398.82	YS33C8-030C 1235.05	YS33S8-030C 1504.41	1	0	104
4	YS23C8-040C 1981.90	YS23S8-040C 2183.91	YS33C8-040C 2131.87	YS33S8-040C 2349.21	1	0	104

PVC Gray - True Union Socket Ends

Size	EPDM PVC Screen	EPDM SS Screen	Viton® PVC Screen	Viton® SS Screen	Std Pk	Mstr Pk	Disc Code
1/2	YS2AP8-005 87.05	YS2AS8-005 172.23	YS3AP8-005 95.07	YS3AS8-005 189.26	1	12	102
3/4	YS2AP8-007 97.24	YS2AS8-007 196.96	YS3AP8-007 107.16	YS3AS8-007 222.17	1	8	102

Schedule 80 CPVC Industrial Products & Accessories
Y-Strainers



Socket



Flanged



SR Thread



True Union

Part numbers shown reflect a mesh size of 8. For different mesh sizes, substitute Mesh Code in part number as specified in chart below.

U.S. Standard Mesh Sieve No.	Sieve Opening Size (in.)	Part Number Mesh Code
8	0.094	8
12	0.062	12
20	0.033	20
30	0.024	30

Example: for 8 Mesh, specify

YS22C8-005C

Additional Mesh Sizes available on request.

Pressure Rating @ 73°F (23°C), Water

1/2" - 2" 150 psi

3" - 4" 90 psi

Maximum Service Temperature

CPVC = 200°F (93°C)

**Temperature/Pressure
De-ratings Apply**



**Schedule 80 CPVC Industrial Products & Accessories
Y-Strainers & True Union Y-Strainers**

CPVC - Socket Ends

Size	EPDM Seals CPVC Screen	EPDM Seals SS Screen	Viton® Seals CPVC Screen	Viton® Seals SS Screen	Std Pk	Mstr Pk	Disc Code
1/2	YS22C8-005C 220.59	YS22S8-005C 303.17	YS32C8-005C 247.02	YS32S8-005C 340.78	1	18	104
3/4	YS22C8-007C 242.37	YS22S8-007C 344.78	YS32C8-007C 272.87	YS32S8-007C 387.53	1	18	104
1	YS22C8-010C 307.98	YS22S8-010C 426.45	YS32C8-010C 346.91	YS32S8-010C 478.56	1	12	104
1-1/4	YS22C8-012C 447.09	YS22S8-012C 615.30	YS32C8-012C 538.04	YS32S8-012C 651.54	1	8	104
1-1/2	YS22C8-015C 480.24	YS22S8-015C 635.59	YS32C8-015C 558.20	YS32S8-015C 710.62	1	8	104
2	YS22C8-020C 679.96	YS22S8-020C 796.78	YS32C8-020C 718.49	YS32S8-020C 869.04	1	4	104
3	YS22C8-030C 811.12	YS22S8-030C 970.28	YS32C8-030C 855.51	YS32S8-030C 1043.76	1	0	104
4	YS22C8-040C 1404.94	YS22S8-040C 1606.94	YS32C8-040C 1510.53	YS32S8-040C 1727.84	1	0	104

CPVC - SR Threaded Ends

Size	EPDM Seals CPVC Screen	EPDM Seals SS Screen	Viton® Seals CPVC Screen	Viton® Seals SS Screen	Std Pk	Mstr Pk	Disc Code
1/2	YS21C8-005CSR 228.62	YS21S8-005CSR 311.20	YS31C8-005CSR 255.06	YS31S8-005CSR 348.82	1	18	104
3/4	YS21C8-007CSR 250.97	YS21S8-007CSR 353.36	YS31C8-007CSR 281.46	YS31S8-007CSR 396.13	1	12	104
1	YS21C8-010CSR 327.67	YS21S8-010CSR 446.11	YS31C8-010CSR 366.61	YS31S8-010CSR 498.21	1	8	104
1-1/4	YS21C8-012CSR 467.31	YS21S8-012CSR 600.88	YS31C8-012CSR 558.27	YS31S8-012CSR 671.79	1	8	104
1-1/2	YS21C8-015CSR 503.66	YS21S8-015CSR 659.00	YS31C8-015CSR 634.34	YS31S8-015CSR 734.02	1	4	104
2	YS21C8-020CSR 713.31	YS21S8-020CSR 830.13	YS31C8-020CSR 799.53	YS31S8-020CSR 902.36	1	0	104
3	YS21C8-030CSR 852.44	YS21S8-030CSR 1011.61	YS31C8-030CSR 912.14	YS31S8-030CSR 1085.07	1	0	104
4	YS21C8-040CSR 1447.78	YS21S8-040CSR 1649.81	YS31C8-040CSR 1553.38	YS31S8-040CSR 1770.71	1	0	104

CPVC - Flanged Ends

Size	EPDM Seals CPVC Screen	EPDM Seals SS Screen	Viton® Seals CPVC Screen	Viton® Seals SS Screen	Std Pk	Mstr Pk	Disc Code
1/2	YS23C8-005C 355.72	YS23S8-005C 436.73	YS33C8-005C 394.83	YS33S8-005C 487.23	1	8	104
3/4	YS23C8-007C 377.84	YS23S8-007C 464.59	YS33C8-007C 409.73	YS33S8-007C 518.49	1	8	104
1	YS23C8-010C 403.47	YS23S8-010C 516.20	YS33C8-010C 439.53	YS33S8-010C 575.49	1	8	104
1-1/4	YS23C8-012C 646.77	YS23S8-012C 796.18	YS33C8-012C 705.09	YS33S8-012C 886.56	1	4	104
1-1/2	YS23C8-015C 720.76	YS23S8-015C 884.65	YS33C8-015C 800.28	YS33S8-015C 986.94	1	4	104
2	YS23C8-020C 906.18	YS23S8-020C 1106.13	YS33C8-020C 994.34	YS33S8-020C 1157.39	1	0	104
3	YS23C8-030C 1238.11	YS23S8-030C 1398.82	YS33C8-030C 1235.05	YS33S8-030C 1504.41	1	0	104
4	YS23C8-040C 1981.90	YS23S8-040C 2183.91	YS33C8-040C 2131.87	YS33S8-040C 2349.21	1	0	104

CPVC - True Union Socket Ends

Size	EPDM CPVC Screen	EPDM SS Screen	Viton® CPVC Screen	Viton® SS Screen	Std Pk	Mstr Pk	Disc Code
1/2	YS2AC8-005C 232.21	YS2AS8-005C 319.13	YS3AC8-005C 260.05	YS3AS8-005C 358.71	1	12	104
3/4	YS2AC8-007C 255.13	YS2AS8-007C 362.93	YS3AC8-007C 287.23	YS3AS8-007C 407.93	1	8	104
1	YS2AC8-010C 324.19	YS2AS8-010C 448.91	YS3AC8-010C 365.18	YS3AS8-010C 503.73	1	8	104
1-1/4	YS2AC8-012C 470.62	YS2AS8-012C 647.68	YS3AC8-012C 566.34	YS3AS8-012C 686.81	1	4	104
1-1/2	YS2AC8-015C 505.52	YS2AS8-015C 669.03	YS3AC8-015C 587.61	YS3AS8-015C 748.01	1	0	104
2	YS2AC8-020C 715.74	YS2AS8-020C 838.71	YS3AC8-020C 756.31	YS3AS8-020C 914.78	1	0	104
3	YS2AC8-030C 853.80	YS2AS8-030C 1021.37	YS3AC8-030C 916.66	YS3AS8-030C 1098.68	1	0	104