

Part No: YS22P8-005CL

Filters & Strainers

Y-Strainers

Desc: 1/2 PVC CL Y STRAINER SOC EPDM P8 MESH

MSRP: 146.18

Part Code: 103

Weight(lbs): 0.254

Weight(kg): 0.115

Weight(gm): 115

Size: 1/2"

Color: CLEAR

Material: PVC



Connection Socket

O-Ring EPDM

Mesh Sieve # 8

Body Color Clear

A = 3- 1/16

A1 = 4- 5/8

B = 1- 5/8

C = 3- 3/8

D = 2- 1/2

E = 1- 5/8

Cv = 5.5
Values

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; ± 1/32 inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; ± 1/32 inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; ± 1/32 inch

L = Overall length of fittings; ± 1/16 inch.

M = Outside diameter of socket/thread hub; ± 1/16 inch.

N = Socket bottom to socket bottom; couplings; ± 1/16 inch.

W = Height of cap; ± 1/16 inch

Typical Molded Dimension References

