

Part No: YS23S8-005CL

Filters & Strainers

Y-Strainers

Desc: 1/2 PVC CL Y-STRAINER FLANGED EPDM S8MSH

MSRP: 404.14

Part Code: 103

Weight(lbs): 0.697

Weight(kg): 0.316

Weight(gm): 316

Size: 1/2"

Color: CLEAR


Material: PVC

Connection Flanged

O-Ring EPDM

Mesh Sieve # 8

Body Color Clear



A = 3- 1/16

A1 = 6

B = 5- 3/4

C = 3-17/32

D = 2- 1/2

E = 1- 5/8

Cv = 5.5
Values

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; ± 1/32 inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; ± 1/32 inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; ± 1/32 inch

L = Overall length of fittings; ± 1/16 inch.

M = Outside diameter of socket/thread hub; ± 1/16 inch.

N = Socket bottom to socket bottom; couplings; ± 1/16 inch.

W = Height of cap; ± 1/16 inch

Typical Molded Dimension References

